

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED8455/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK605

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1404		1997	MHz
Tuning Voltage	0.5		8	V
Power Output		+7		dBm
Phase Noise				
at 1 kHz offset		-69		dBc/Hz
at 10 KHz offset		-92		dBc/Hz
at 100 KHz offset		-112		dBc/Hz
at 1000 kHz offset		-135		dBc/Hz
Pulling at 12 dB _r PK-PK all phases		28		MHz
Pushing at V _{cc} =5V±0.25V		5		MHz/V
Tuning Sensitivity		88 - 103		MHz/V
Harmonic Suppression		-20		dBc
3 dB Modulation Bandwidth		2500		kHz
Supply Voltage		4.5		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (V _{cc})	+6.5V
Absolute Tuning Voltage (V _{tune})	+10V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16