

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED9726/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK605

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1780		2180	MHz
Tuning Voltage	0.5		4.5	V
Power Output		0		dBm
Phase Noise				
at 1 kHz offset		-65		dBc/Hz
at 10 KHz offset		-90		dBc/Hz
at 100 KHz offset		-110		dBc/Hz
at 1000 kHz offset		-130		dBc/Hz
Pulling at 12 dB PK-PK all phases		7.5		MHz
Pushing at Vcc=5V±0.25V		5		MHz/V
Tuning Sensitivity		150 - 195		MHz/V
Harmonic Suppression		-15		dBc
3 dB Modulation Bandwidth		9100		kHz
Supply Voltage		5		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+6.5V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16