

Plug-In Frequency Mixer

SBL-3+

Level 7 (LO Power +7 dBm) 0.025 to 200 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	8
RF	1
IF	3,4 [^]
GROUND	2,5,6,7
CASE GROUND	2

[^] pins must be connected together externally

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F
.770	.800	.285	.310	.370	.400
19.56	20.32	7.24	7.87	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

Features

- excellent conversion loss, 4.81 dB typ.
- high L-R isolation, 45 dB typ. L-I isolation, 40 dB typ.
- rugged welded construction

Applications

- VHF
- defense & federal communications



Generic photo used for illustration purposes only

CASE STYLE: A06

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)					
LO/RF f_L - f_U	IF	Mid-Band m		Total Range Max.		L		M		U		L		M		U	
		$\bar{X}$	σ	Max.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
.025-200	DC-200	4.81	.05	7.5	8.5	55	50	45	30	35	25	45	35	40	30	30	20


1 dB COMP.: +1 dBm typ.

L = low range [f_L to 10 f_L] M = mid range [10 f_L to $f_U/2$] U = upper range [$f_U/2$ to f_U]
m= mid band [$2f_L$ to $f_U/2$]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO					
		LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
0.03	30.03	8.41	70.32	73.42	1.44	1.33
0.04	30.04	6.80	68.24	73.04	1.45	1.32
0.05	30.05	6.31	68.06	73.56	1.45	1.29
0.10	30.10	5.51	67.57	74.37	1.44	1.28
0.20	30.20	5.27	67.72	74.82	1.43	1.34
0.50	30.50	5.15	67.66	75.16	1.43	1.35
1.00	31.00	4.98	67.06	74.46	1.43	1.37
2.00	32.00	4.89	66.83	74.03	1.42	1.37
5.00	35.00	4.86	66.56	72.56	1.40	1.36
10.00	40.00	4.93	66.04	69.54	1.39	1.36
20.00	50.00	5.06	64.65	63.95	1.37	1.35
30.79	60.79	5.13	63.14	60.24	1.35	1.36
38.48	68.48	5.16	62.80	57.90	1.33	1.36
50.00	80.00	5.09	61.63	53.78	1.29	1.39
76.94	46.94	4.97	58.56	48.75	1.26	1.41
100.00	70.00	4.81	58.22	46.67	1.26	1.45
123.09	93.09	4.85	52.38	44.01	1.22	1.49
146.16	116.16	4.94	58.82	46.22	1.19	1.51
176.93	146.93	5.26	51.25	39.55	1.17	1.55
200.00	170.00	5.36	44.86	38.02	1.18	1.60

Electrical Schematic









Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
SBL-3
DJ/TD/CP/AM
200409
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

