


Frequency Mixer

SBL-ED7399/1

Level 16 (LO Power +16 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		900	MHz
	RF (fL to fU)	5		900	MHz
	IF	200		950	MHz
Conversion Loss	mid band		6.1		dB
	Total Range		6.6		dB
LO-RF Isolation	Low Range		-		dB
	Mid Range		61		dB
	Upper Range		43		dB
LO-IF Isolation	Low Range		-		dB
	Mid Range		64		dB
	Upper Range		52		dB

Note: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	8
RF	3, 4 ^
IF	1
GROUND	2, 5, 6, 7

^ - pins must be connected together externally