

Coaxial

Low Pass Filter

50Ω Flat Time Delay DC to 94 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- flat group delay for low pulse distortion
- rugged shielded case
- other SBLP models available with wide selection of cut-off frequencies

Applications

- linear modulation techniques
- voice transmission applications
- digital communications

SBLP-156+ SBLP-156



CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SBLP-156(+)	\$38.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco, MHz Nom.	STOPBAND (MHz)		VSWR (:1)		GROUP DELAY VARIATION (nsec)		
		(loss > 10 dB)	(loss > 20 dB)	DC-0.2fco	DC-0.6fco	DC-fco	DC-2fco	DC-2.67fco
(loss < 1.2 dB) Min.	(loss 3 dB)			$\bar{X}$	$\bar{X}$	$\bar{X}$	$\bar{X}$	$\bar{X}$
DC-94	156	312-416	416	1.3:1	1.1:1	0.3	1.1	1.5



Outline Drawing



Outline Dimensions (inch/mm)




B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{X}$	σ			
1.0	0.05	0.1	35.6	1.0	2.185
32.0	0.17	0.1	17.6	17.0	2.540
48.0	0.30	0.1	14.2	32.0	2.534
63.0	0.46	0.1	11.9	48.0	2.358
79.0	0.68	0.1	10.0	63.0	2.382
94.0	0.92	0.1	8.3	79.0	2.619
95.0	0.93	0.1	8.2	94.0	2.595
136.0	1.98	0.1	4.6	95.0	2.467
156.0	2.79	0.2	3.6	116.0	2.682
157.0	2.85	0.2	3.5	136.0	2.392
202.0	5.33	0.2	2.2	156.0	2.383
246.0	8.75	0.3	1.2	157.0	2.835
268.0	10.25	0.3	0.9	180.0	2.501
290.0	11.57	0.3	0.7	202.0	2.433
312.0	12.97	0.3	0.6	224.0	1.923
313.0	13.03	0.3	0.6	246.0	1.878
343.0	15.67	0.3	0.5	268.0	1.392
372.0	18.60	0.3	0.4	290.0	1.756
387.0	20.01	0.3	0.3	312.0	2.001
402.0	21.23	0.3	0.3	313.0	2.235
416.0	22.25	0.3	0.3	328.0	1.944
417.0	22.32	0.3	0.3	343.0	1.740
481.0	27.17	0.5	0.3	358.0	1.360
545.0	31.67	0.7	0.3	372.0	0.911
609.0	36.32	1.0	0.4	387.0	0.786
673.0	39.65	1.2	0.4	402.0	1.170
705.0	41.78	1.2	0.4	416.0	0.978
737.0	44.07	1.6	0.5	417.0	1.269
769.0	46.28	1.6	0.5	449.0	1.042
800.0	47.95	1.8	0.5	481.0	0.864



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M98898
SBLP-156
070411