

Coaxial

Low Pass Filter

SBLP-200+ SBLP-200

50Ω Flat Time Delay DC to 120 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- flat group delay for low pulse distortion
- rugged shielded case
- other SBLP models available with wide selection of cut-off frequencies

Applications

- linear modulation techniques
- voice transmission applications
- digital communications



CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SBLP-200(+)	\$38.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.


Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco, MHz Nom.	STOPBAND (MHz)		VSWR (:1)		GROUP DELAY VARIATION (nsec)		
		(loss > 10 dB)	(loss > 20 dB)	DC-0.2fco	DC-0.6fco	DC-fco	DC-2fco	DC-2.67fco
(loss < 1.2 dB) Min.	(loss 3 dB)			$\bar{X}$	$\bar{X}$	$\bar{X}$	$\bar{X}$	$\bar{X}$
DC-120	200	400-534	534	1.6:1	1.9:1	0.4	1.3	1.6


Outline Drawing




TYPICAL GROUP DELAY



TYPICAL FREQUENCY RESPONSE INSERTION LOSS



electrical schematic






Outline Dimensions (inch mm)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{X}$	σ			
1.0	0.04	0.1	35.5	1.0	1.829
41.0	0.10	0.1	27.0	21.0	1.915
61.0	0.16	0.1	20.6	41.0	2.140
81.0	0.22	0.1	16.6	61.0	2.006
101.0	0.33	0.1	13.4	81.0	2.109
120.0	0.52	0.1	10.4	101.0	2.087
121.0	0.53	0.1	10.2	120.0	2.170
174.0	2.10	0.1	4.7	121.0	2.113
200.0	3.22	0.1	3.5	148.0	2.521
201.0	3.26	0.1	3.5	174.0	2.169
258.0	6.65	0.2	1.6	200.0	1.964
315.0	9.45	0.2	0.9	201.0	2.367
344.0	11.17	0.3	0.7	230.0	1.912
372.0	13.45	0.4	0.5	258.0	1.485
400.0	15.58	0.5	0.4	287.0	1.356
401.0	15.65	0.5	0.4	315.0	2.048
439.0	17.90	0.7	0.3	344.0	2.142
477.0	20.36	0.8	0.3	372.0	1.206
496.0	21.60	0.8	0.2	400.0	0.894
515.0	22.72	0.9	0.2	401.0	1.205
534.0	23.75	0.9	0.2	420.0	1.143
535.0	23.81	0.9	0.2	439.0	0.984
580.0	26.67	1.0	0.2	458.0	1.412
624.0	29.26	1.0	0.2	477.0	0.888
668.0	31.05	1.1	0.2	496.0	0.903
712.0	33.19	1.2	0.3	515.0	1.244
734.0	34.36	1.2	0.3	534.0	1.282
756.0	35.72	1.2	0.3	535.0	0.796
778.0	37.00	1.2	0.3	558.0	1.491
800.0	37.94	1.1	0.3	580.0	0.941



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M98898
SBLP-200
070307