# Surface Mount **RF Transformer**

50Ω 2.6 to 11.0 GHz

# SBTX2-113-2W+

## **The Big Deal**

- Super wideband, 2.6 to 11.0 GHz
- Low insertion loss, 1.4 dB typ.
- Amplitude Unbalance,  $\pm 0.9 \text{ dB typ.}$
- Low phase unbalance,  $\pm 6^{\circ}$  typ.
- Common mode rejection, 22 dB typ.



## **Product Overview**

Mini-Circuits' SBTX2-113-2W+ is a surface-mount transmission line transformer (core and Semi-Rigid cable) covering a very wide frequency range from 2.6 to 11.0 GHz. The transformer provides low insertion loss with excellent phase and amplitude performance. Featuring core and cable construction on a 8-lead PCB unit measures 0.32 x 0.32 x 0.69 accommodating dense circuit board layouts.

## **Key Features**

Feature	Advantages
Wideband, 2.6 to 11.0 GHz	Super wide frequency range covers bandwidth requirements for many broadband applications.
Low insertion loss, 1.4dB	Provides excellent signal transmission from input to output with consistent performance across its entire frequency range.
Good Phase and Amplitude Unbalance	Provides good CMRR and IP2.
Small size (0.32 x 0.32 x 0.69)	Provide good solderability and tight layouts.

# Surface Mount **RF Transformer**

## 50Ω 2.6 to 11.0 GHz 1:2 Ratio

#### Features

- wide bandwidth 2.6 to 11.0 GHz
- unbalanced to balanced transformer
- excellent amplitude and phase unbalance
  aqueous washable

#### Applications

- defense radar
- line of sight links
- PCS
- ation cellular
  - wideband push-pull amplifiersADC (Analog to Digital Converter)
  - Balanced Receivers





Generic photo used for illustration purposes only

CASE STYLE: AH2765

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### Electrical Specifications at 25°C

Parameter	Frequency (GHz)	Min.	Тур.	Max.	Unit
Impedance Ratio (secondary/primary)			2		
Frequency Range		2.6		11.0	GHz
Insertion Loss (Average) (above theoretical 3 dB)	2.6 - 6.0 6.0 - 10.0 10.0 - 11.0		1.4 1.5 1.7	1.9 2.2 2.5	dB
Amplitude Unbalance (±)	2.6 - 11.0 4.0 - 9.0	_	0.9 0.7	1.3 1.0	dB
Phase Unbalance (±)	4.0 - 9.0 2.6 - 11.0		4 6	8 12	Degree
Common mode rejection	4.0 - 9.0 2.6 - 11.0	18 15	24 22		dB

#### **Maximum Ratings**

Parameter	Ratings	
Operating Temperature	-40°C to 85°C	
Storage Temperature -55°C to 100°C		
RF Power	2W	

Permanent damage may occur if any of these limits are exceeded.

#### **Pin Connections**


Function	Pin Number		
PRIMARY DOT	7		
PRIMARY (GND) 6,8			
SECONDARY DOT	4		
SECONDARY	2		
GND	1,3,5,6,8		

Config. G




# SBTX2-113-2W+

#### **Outline Drawing**





#### Demo Board MCL P/N: TB-1081+ Suggested PCB Layout (PL-629)



#### **Typical Performance Data**

Frequency (MHz)	Avg. Insertion Loss (dB)	CMRR (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
2600	0.73	17.53	2.01	7.61
3000	0.60	19.42	1.61	6.14
3400	0.53	21.49	1.28	4.73
5000	0.89	34.90	0.28	0.93
5500	1.11	53.33	0.02	0.20
6000	1.26	32.59	0.28	1.96
6500	1.27	29.02	0.44	2.86
8000	1.21	30.85	0.12	3.19
9000	1.21	41.17	0.15	0.16
10000	1.14	31.62	0.09	2.95
11000	1.44	32.11	0.42	0.69





#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

