

Power Splitter/Combiner 4 Way-Quadrifilar

SCQA-ED16134/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : CK1704

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		600		1000 MHz
Isolation	600-1000 MHz		18	dB
Insertion Loss Above 6 dB	600-1000 MHz		2.0	dB
Phase Unbalance	600-1000 MHz		5.0	dB
Amplitude Unbalance	600-1000 MHz		0.80	(:1)
	SUM PORT		1.40	(:1)
	OUTPUT PORTS		1.20	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	10
PORT 1 (0°)	1
PORT 2 (90°)	2
PORT 3 (180°)	3
PORT 4 (270°)	4
GND EXT	5,6,7,8,9,11,12

Functional Diagram

