DC Pass **Power Splitter/Combiner**

SEPS-2-63+

2 Way-0° 50Ω 680 to 6000 MHz

The Big Deal

- >3 octave bandwidth, 680 to 6000 MHz
- Low insertion loss, 1.0 dB
- Small size, 1.25 x 1.0 x 0.2"



CASE STYLE: JF1258

Product Overview

Mini-Circuits' SEPS-2-63+ is a 50Ω 2-way 0° surface mount splitter/combiner covering the 680 to 6000 MHz frequency range, supporting a wide variety of applications. This model can handle up to 5W RF input power as a splitter and provides low insertion loss, low phase and amplitude unbalance, and good isolation. Housed in a miniature, shielded package (1.25 x 1.0 x 0.2") with wrap-around terminations this unit interfaces with gold over nickel plate termination finish.

Key Features

Feature	Advantages				
Wideband, 680 to 6000 MHz	>3 octave bandwidth supports a wide range of broadband applications.				
Low insertion loss, 1.0 dB	The combination of 5W power handling and low insertion loss makes this model a suit- able candidate for distributing signals while maintaining signal power.				
Low unbalance: • 0.2 dB amplitude unbalance • 1.5° phase unbalance	SEPS-2-63+ produces nearly equal output signals, ideal for parallel path / multichannel systems.				
Good isolation, 22 dB	Minimizes interference between input ports.				
Good output matching VSWR, 1.3:1 typ.	Provides excellent thru-path transmission with low signal reflection.				
Small size, 1.25 x 1.0 x 0.2"	Saves space in crowded PCB layouts.				

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

DC Pass **Power Splitter/Combiner**

2 Way-0° 680 to 6000 MHz 50Ω


Maximum Ratings

Operating Temp	-40°C to 85°C				
Storage Temper	-55°C to 100°C				
Power Input (as	5W max.				
Internal Dissipation		0.4W max.			
DC Current	mA for each port)				
Permanent damage may occur if any of these limits are exceeded.					

Pin Connections

SUM PORT	17
PORT 1	4
PORT 2	8
GROUND	all others


Outline Drawing SIDE VIEW



Outline Dimensions (inch)

	N 11111					
G	F	E	D	С	В	Α
.040	.060	.100	.125	.200	1.000	1.250
1.02	1.52	2.54	3.18	5.08	25.40	31.75
wt		М	L	к	J	н
grams		.920	.060	.050		
4.4		23.37	1.52	1.27		

Demo Board MCL P/N: TB-760+ Suggested PCB Layout (PL-402)



Notes

Features

- wideband 680-6000 MHz
- good output matching, VSWR 1.3 typ.
- excellent amplitude unbalance, 0.2 dB typ.

Applications

- SATCOM broadband wireless
- · test and measurement
- wireless telecom

SEPS-2-63+




Generic photo used for illustration purposes only CASE STYLE: JF1258

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		680		6000	MHz	
Insertion Loss Above 3.0 dB	680 - 1200	_	0.6	1.0		
	1200 - 5000	_	0.8	1.5	dB	
	5000 - 6000	_	1.0	2.5		
Isolation	680 - 1200	10	17.0	_	dB	
	1200 - 6000	17	22.0	_		
Phase Unbalance	680 - 1200	_	0.3	2.0	Degree	
	1200 - 6000	_	1.5	5.0		
Amplitude Unbalance	680 - 1200	-	0.1	0.4	dB	
	1200 - 6000	_	0.2	0.6		
VSWR (Port S)	680 - 1200	_	1.6	2.0	:1	
	1200 - 6000	_	1.5	1.82		
VSWR (Port 1-2)	680 - 6000	_	1.3	1.6	:1	

Electrical Schematic



A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

REV OR M157142 SEPS-2-63+ ED-16030401 PW/CP/AM 200811 Page 2 of 3





SEPS-2-63+


Frequency (MHz)	Total (d	Loss¹ B)	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2			,			
680	3.47	3.43	0.04	11.58	0.27	1.75	1.18	1.15
700	3.46	3.42	0.04	11.91	0.26	1.74	1.17	1.15
800	3.43	3.37	0.05	13.63	0.18	1.67	1.18	1.16
900	3.39	3.32	0.07	15.47	0.10	1.59	1.19	1.19
1000	3.35	3.28	0.07	17.43	0.01	1.51	1.20	1.21
1500	3.22	3.17	0.04	23.19	0.01	1.14	1.14	1.17
2000	3.24	3.21	0.04	20.82	0.01	1.16	1.03	1.01
2500	3.37	3.31	0.06	23.43	0.21	1.34	1.14	1.18
3000	3.49	3.44	0.06	24.53	0.12	1.42	1.28	1.33
3500	3.38	3.37	0.01	22.04	0.18	1.23	1.21	1.23
4000	3.44	3.37	0.07	23.97	0.36	1.14	1.06	1.09
4500	3.66	3.57	0.09	30.87	0.11	1.34	1.19	1.24
5000	3.67	3.69	0.02	21.15	0.12	1.36	1.18	1.22
5500	4.08	4.03	0.05	21.83	0.41	1.26	1.13	1.19
6000	4.71	4.61	0.10	28.30	0.21	1.61	1.32	1.31

Typical Performance Data

1. Total Loss = Insertion Loss + 3dB splitter theoretical loss.







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

###