

SMA/BNC

Adaptenuator

50Ω 0.5W 3dB DC to 2000 MHz


Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 150°C

Permanent damage may occur if any of these limits are exceeded.


Outline Drawing



Outline Dimensions (inch/mm)

B	D	wt
.61	1.69	grams
15.49	42.93	24.0

Electrical Schematic



Features

- improved interface matching
- wideband, DC to 2000 MHz, useable to 4000 MHz
- excellent VSWR, 1.1:1 typ.
- excellent flatness, ± 0.1 dB typ.
- rugged unibody construction

Applications

- instrumentation
- provides attenuation and connector type change
- minimizes hardware

SF-BM-3+



CASE STYLE: DJ870

Connectors	Model
Conn1 SMA-Female	Conn2 BNC-Male
SF-BM-3+	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications

FREQ. (MHz)	ATTENUATION (dB)								VSWR (:1)						MAX. INPUT POWER (W)
	Flatness*														
	DC-500 MHz			DC-1000 MHz			DC-2000 MHz		DC-500 MHz		DC-1000 MHz		DC-2000 MHz		
	Nom.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.		
f _L -f _U															
DC-2000	3±0.3	0.05	0.15	0.10	0.20	0.15	0.25	1.1	1.2	1.1	1.2	1.2	1.25	0.5	

*Flatness defined as peak to peak attenuation over band divided by 2.

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)	
		BNC-Male	SMA-Female
1.00	3.01	1.00	1.00
5.00	3.01	1.00	1.00
10.00	2.99	1.00	1.00
50.00	3.02	1.00	1.01
100.00	3.00	1.01	1.01
500.00	3.07	1.03	1.04
1000.00	3.13	1.05	1.06
1500.00	3.16	1.05	1.07
1700.00	3.17	1.04	1.06
2000.00	3.20	1.05	1.06



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
M160892
EE-9890
SF-BM-3+
URJ/TD/CP/AM
170512