Coaxial **High Pass Filter**

50Ω 48 to 2150 MHz

The Big Deal

- Low insertion loss
- High rejection
- Connectorized package

SHP-48+



Generic photo used for illustration purposes only CASE STYLE: FF56

Product Overview

SHP-48+ is a High pass filter in a connectorized package covering 48 to 2150 MHz. This filter can be used in SATCOM, CATV, Broadband Fiber Networks and Multiband radio systems. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages		
Low insertion loss	Can be used in high performance applications.		
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad band frequency.		
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.		

Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Coaxial **High Pass Filter**

50Ω 48 to 2150 MHz

• Wide band, 48 MHz to 2150 MHz

SHP-48+



Generic photo used for illustration purposes only CASE STYLE: FF56 Connectors Model SMA-M\F SHP-48+

Electrical Specifications at 25°C

Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
Stop Bond	Rejection Loss	DC-F1	DC-18	20	31	-	dB
Stop Banu	VSWR	DC-F1	DC-18	-	40	-	:1
Deee Bend	Insertion Loss	F2-F3	48-2150	-	0.6	1.2	dB
Pass band	VSWR	F2-F3	48-2150	-	1.15	-	:1



Features

High rejection

- SATCOM
- Broadband Fiber Networks

Connectorized package

- CATV
- Radio communications
- Receivers \ transmitters

Functional Schematic



Typical Frequency Response





Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	0.5 W.					
	6 1 1 1 1					

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency	Insertion Loss	VSWB
(MHz)	(dB)	(:1)
0.5	94.13	1737.18
5.5	83.29	868.59
8.5	64.96	434.30
12.0	49.88	217.15
18.0	31.26	82.73
24.0	17.08	26.33
28.0	9.38	10.07
31.0	5.06	4.54
34.0	2.54	2.32
39.0	1.08	1.23
48.0	0.59	1.06
57.0	0.43	1.05
63.0	0.37	1.06
74.0	0.30	1.10
96.0	0.23	1.15
150.0	0.15	1.14
340.0	0.10	1.07
1150.0	0.18	1.04
1900.0	0.26	1.09
2150.0	0.31	1.11





A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

1.0

0.1

∭Mini-Circuits

10.0

100.0 FREQUENCY (MHz) 10000.0

1000.0

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B ECO-005139 SHP-48+ EDU1367 URJ 201201 Page 2 of 3

SHP-48+

Coaxial Connections

INPUT SMA-Male OUTPUT SMA-Female

Outline Drawing



Outline Dimensions (inch)

wt	Е	D	В
grams	0.312	1.70	0.43
18.0	7.92	43.18	10.92

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits