

Frequency Mixer

SIM-ED12399/11

Level 10 (LO Power + 10 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : HV1195

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	2240		8060	MHz
	RF (f _L to f _U)	2240		8060	MHz
	IF	10		3000	MHz
Conversion Loss	Total Range		6.3		dB
LO-RF Isolation			29		dB
LO-IF Isolation			25		dB
Input IP3			+15		dBm
1 dB Compression			+5		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	8
RF	4
IF	2
GROUND	1,3,5,6,7

Electrical Schematics

