

Power Splitter/Combiner

2 Way-0°

SP-ED12593/3

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CA531

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		3300		3600 MHz
Isolation	3300 - 3600 MHz		20	dB
Insertion Loss Above 3.0 dB	3300 - 3600 MHz		0.50	dB
Phase Unbalance	3300 - 3600 MHz		1.559	deg.
Amplitude Unbalance	3300 - 3600 MHz		0.005	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.25	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Functional Diagram

