

Non-Catalog Model

Frequency Mixer

SRA-2500SH

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



CASE STYLE : A06

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		2500	MHz
	RF (fL to fU)	5		2500	MHz
	IF	1		1000	MHz
Conversion Loss	mid band		5.8	7.5	dB
	Total Range			10.5	dB
LO-RF Isolation	Low Range	25	40		dB
	Mid Range	28	37		dB
	Upper Range	18	30		dB
LO-IF Isolation	Low Range	35	50		dB
	Mid Range	25	42		dB
	Upper Range	17	25		dB
IP3 Input			+28		dBm
1 dB Comp. Input Power			+14		dBm


Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	-

Electrical Schematics



PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally