## Surface Mount **Bandpass Filter**

## SXBP-70W+

 $50\Omega$ 50 to 90 MHz

## The Big Deal

- Very low insertion loss, 0.5dB typical
- Good VSWR, 1.3:1 typical
- Flat group delay response, 2 ns typical
- Miniature shielded package



Generic photo used for illustration purposes only CASE STYLE: HF1139

### **Product Overview**

SXBP-70W+ is a  $50\Omega$  bandpass filter in a shielded package fabricated using SMT technology. This bandpass filter covers from 50 to 90 MHz. This filter build with high Q capacitors and wire welded inductors for high reliability. This filter has sharper cut-off and well suited for IF signal processing applications.

### **Key Features**

Feature	Advantages
Very low insertion loss, 0.5 dB typical	Can be used in telecommunication and broadband wireless application.
Good rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band.
Shielded package	The small surface mount package enables the SXBP-70W+ to be used in compact design

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

 $50\Omega$ 50 to 90 MHz

### SXBP-70W+



Generic photo used for illustration purposes only CASE STYLE: HF1139


#### **Features**

- IF Frequency
- Very low insertion loss, 0.5 dB typical
- Flat group delay response, 2 ns typical
- · Miniature shielded package


#### **Applications**

- · Satellite base station
- · IF signal processing
- · Military hi-rel systems
- · Harmonic rejection

### **Functional Schematic**



### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications at 25°C


·							
Parai	Parameter		Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	70	_	MHz
Pass Band	Insertion Loss	F1-F2	50-90	_	0.5	1.0	dB
	VSWR	F1-F2	50-90	_	1.3	1.7	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-2	10	14	_	dB
Stop Ballu, Lower	VSWR	DC-F3	DC-2	_	20	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	137-1500	20	23	_	dB
Stop Ballu, Opper	VSWR	F4-F5	137-1500	_	20	_	:1


Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	0.5W			


Permanent damage may occur if any of these limits are exceeded.


### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	21.14	103.07	50	5.29
2	15.26	61.74	52	5.30
2 3	11.91	38.00	54	5.32
4	9.63	25.35	56	5.31
5 6	7.95	18.09	58	5.38
6	6.65	13.62	60	5.41
11	3.11	5.43	62	5.44
50	0.18	1.21	64	5.55
70	0.23	1.12	66	5.61
90	0.41	1.23	68	5.68
100	0.54	1.24	70	5.77
124	3.38	2.57	72	5.86
130	10.52	8.60	74	5.95
135	20.24	18.34	76	6.12
137	24.88	22.39	78	6.24
139	30.16	26.24	80	6.38
140	33.15	28.19	82	6.54
500	44.54	122.40	84	6.71
1250	41.34	83.38	86	6.90
1500	30.88	13.12	90	7.35









Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




#### **Pad Connections**

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7


#### Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



- 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
  FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



### **Outline Drawing**



#### Outline Dimensions (inch )

G	F	E	D	С	В	Α
.040	.060	.07	.200	.27	.74	.44
1.02	1.52	1.78	5.08	6.86	18.80	11.18
wt		M	L	K	J	Н
grams		.060	.055	.470	.200	.660
3.0		1.52	1.40	11.94	5.08	16.76

Note: Please refer to case style drawing for details

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

