

Engineering Development Model

Voltage Controlled Oscillator

ROS-EDR7804/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK1113

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	5223		5363	MHz
Tuning Voltage	0.5		4.9	V
Power Output	+1	+3	+5	dBm
Phase Noise				
at 1 kHz offset		-74		dBc/Hz
at 10 KHz offset		-102		dBc/Hz
at 100 KHz offset		-122		dBc/Hz
at 1000 kHz offset		-140		dBc/Hz
Pulling at 12 dBr PK-PK all phases			15	MHz
Pushing at Vcc=5V±0.25V			5	MHz/V
Tuning Sensitivity		20-80		MHz/V
Harmonic Suppression			-15	dBc
3 dB Modulation Bandwidth		2000		kHz
Supply Voltage		5		V
Supply Current			35	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 75°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+7V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16