

Engineering Development Model

Voltage Controlled Oscillator

ROS-EDR8253

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CK1113

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	3619		3711	MHz
Tuning Voltage	0.1		16	V
Power Output	+3	+5	+7	dBm
Phase Noise				
at 1 kHz offset		-77		dBc/Hz
at 10 KHz offset		-102		dBc/Hz
at 100 KHz offset		-124		dBc/Hz
at 1000 kHz offset		-144		dBc/Hz
Pulling at 12 dBr PK-PK all phases			5	MHz
Pushing at Vcc=5V±0.25V			2	MHz/V
Tuning Sensitivity		7		MHz/V
Harmonic Suppression			-5	dBc
Supply Voltage		8		V
Supply Current		30	40	mA

MAXIMUM RATINGS	
Operating Temperature	-33°C to 80°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+10V
Absolute Tuning Voltage (Vtune)	+20V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16