

Frequency Mixer

SYM-ED14819/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TTT881

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _u)	1860		2930	MHz
	RF (f _L to f _u)	10		1080	MHz
	IF	640		1900	MHz
Conversion Loss	Total Range		8.2		dB
LO-RF Isolation			26		dB
LO-IF Isolation			32		dB
Input IP3			+24		dBm
1 dB Compression			+14		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C TO +85°C
Storage Temperature	-55°C TO +100°C

PIN CONNECTIONS	
LO	2
RF	3
IF	1
GROUND	4,5,6