


Engineering Development Model

Voltage Controlled Oscillator

ROSA-ED9946/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-481

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1835		1837	MHz
Tuning Voltage	1.5		9.5	V
Power Output		4.3		dBm
Phase Noise				
at 1 kHz offset		-88		dBc/Hz
at 10 KHz offset		-112		dBc/Hz
at 100 KHz offset		-132		dBc/Hz
at 1000 kHz offset		-152		dBc/Hz
Pulling at 12 dBm PK-PK all phases		1.2		MHz
Pushing at Vcc ± 5%		.5		MHz/V
Tuning Sensitivity		2-3		MHz/V
Harmonic Suppression		-27		dBc
3 dB Modulation Bandwidth		2,800		kHz
Supply Voltage		11		V
Supply Current			40	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+12V
Absolute Tuning Voltage (Vtune)	+11.5V

PIN CONNECTIONS	
RF OUT	1
VCC	4
V-TUNE	16
GROUND	2,3,5,6,7,8,9,10,11,12,13,14,15

