

# Surface Mount Power Splitter/Combiner

## SBB-2-13 SBB-2-13+

2 Way-0° 50Ω 950 to 1300 MHz



CASE STYLE: SM31

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.25W max.

Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

SUM PORT	2
PORT 1	6
PORT 2	4
GROUND	1,3,5

### Outline Drawing




### PCB Land Pattern



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
.200	.200	.070	.275	.050	.015	.050	.085	.006	.019
5.08	5.08	1.78	6.99	1.27	0.38	1.27	2.16	0.15	0.48
L	M	N	P	Q	R	S	T	wt	
.300	.064	.022	.032	-.014	.030	.094		grams	
7.62	1.63	0.56	0.81	-	0.36	0.76	2.39	0.1	

### Demo Board MCL P/N: TB-156 Suggested PCB Layout (PL-003)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
    - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
    - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- very stable performance over temp. range
- excellent insertion loss, 0.6 dB typ.
- excellent isolation, 24 dB typ.
- solder plated leads for excellent solderability and strain relief
- small size, 0.2"X0.275"X0.07"
- very low cost
- aqueous washable
- protected by U.S Patent, 6,819,202

### Applications

- satellite communications
- aeronautical

### Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION <sup>2</sup> (dB)		INSERTION LOSS <sup>1</sup> (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
	Typ.	Min.	Typ.	Max.	Max.	Max.
f <sub>L</sub> -f <sub>U</sub>						
950-1300	24	15	0.6	1.3	3.0	0.6

1. Includes test fixture losses
2. Isolation degrades to 12 dB min from 1200 to 1300 MHz.

### Typical Performance Data

Frequency (MHz)	Total Loss <sup>1</sup> (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
950.00	3.49	3.47	0.02	24.74	0.59	1.16	1.07	1.03
960.00	3.49	3.47	0.02	25.72	0.59	1.15	1.07	1.03
970.00	3.49	3.47	0.02	26.78	0.61	1.13	1.07	1.03
980.00	3.50	3.47	0.02	27.95	0.62	1.12	1.07	1.03
990.00	3.50	3.48	0.02	29.24	0.63	1.10	1.07	1.03
1000.00	3.50	3.48	0.02	30.61	0.63	1.09	1.07	1.03
1010.00	3.51	3.48	0.02	31.95	0.63	1.07	1.07	1.03
1050.00	3.54	3.51	0.03	32.06	0.63	1.04	1.08	1.04
1100.00	3.59	3.56	0.03	25.59	0.65	1.10	1.09	1.06
1150.00	3.66	3.63	0.03	21.31	0.65	1.20	1.12	1.08
1250.00	3.88	3.87	0.02	16.11	0.69	1.46	1.19	1.16
1260.00	3.91	3.90	0.02	15.72	0.68	1.49	1.20	1.17
1280.00	3.97	3.96	0.01	14.99	0.69	1.55	1.22	1.19
1290.00	4.01	4.00	0.01	14.65	0.70	1.59	1.23	1.20
1300.00	4.04	4.04	0.00	14.32	0.72	1.62	1.24	1.21

1. Total Loss = Insertion Loss + 3dB splitter loss.



### electrical schematic

