

Low Pass Filter

SBLP-300+

50Ω Flat Time Delay DC to 180 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- flat group delay for low pulse distortion
- rugged shielded case
- other SBLP models available with wide selection of cut-off frequencies

Applications

- linear modulation techniques
- voice transmission applications
- digital communications



Generic photo used for illustration purposes only

CASE STYLE: FF99


 Connectors Model
SMA SBLP-300+
+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications

PASSBAND (MHz)	fco, MHz Nom.	STOPBAND (MHz)		VSWR (:1)		GROUP DELAY VARIATION (nsec)		
		(loss > 10 dB)	(loss > 20 dB)	DC-0.2fco	DC-0.6fco	DC-fco	DC-2fco	DC-2.67fco
(loss < 1.2 dB) Min.	(loss 3 dB)			X	X	X	X	X
DC-180	300	600-801	801	1.25:1	2.2:1	0.2	0.6	0.8


Outline Drawing



TYPICAL GROUP DELAY


 TYPICAL FREQUENCY RESPONSE
 INSERTION LOSS


electrical schematic






Outline Dimensions (inch mm)

B	D	E	WT GRAMS
.70	1.98	.312	42.0
(17.78)	(50.29)	(7.92)	

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ			
10.0	0.16	0.2	30.7	10.0	1.563
67.0	0.27	0.2	16.4	39.0	1.282
95.0	0.37	0.1	13.4	67.0	1.509
124.0	0.53	0.1	11.1	95.0	1.368
152.0	0.73	0.1	9.4	124.0	1.468
180.0	0.99	0.1	7.9	125.0	1.487
200.0	1.24	0.1	7.1	180.0	1.297
267.0	2.35	0.2	4.9	200.0	1.351
300.0	3.06	0.2	4.1	234.0	1.343
400.0	5.85	0.2	2.5	267.0	1.534
458.0	7.82	0.2	1.8	300.0	1.427
515.0	9.91	0.3	1.3	400.0	1.383
543.0	11.02	0.4	1.1	429.0	1.448
572.0	12.18	0.4	0.9	458.0	0.984
600.0	13.35	0.5	0.8	486.0	1.599
700.0	17.70	0.5	0.5	515.0	1.173
729.0	18.96	0.6	0.5	543.0	1.140
758.0	20.25	0.6	0.5	572.0	1.134
773.0	20.92	0.6	0.5	600.0	0.869
787.0	21.51	0.6	0.5	700.0	0.878
801.0	22.10	0.6	0.5	715.0	0.983
900.0	26.28	0.7	0.6	729.0	0.767
950.0	28.25	0.7	0.7	744.0	1.244
1000.0	30.16	0.8	0.8	758.0	0.807
1050.0	32.02	0.9	0.8	773.0	1.089
1100.0	33.74	0.9	0.9	787.0	1.144
1125.0	34.62	1.1	0.9	801.0	0.587
1150.0	35.50	1.2	1.0	900.0	0.940
1175.0	36.29	1.2	1.0	925.0	0.980
1200.0	37.10	1.4	1.0	950.0	0.475



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

