Bandpass Filter

SBP-29+

 50Ω 24 to 35 MHz



Generic photo used for illustration purposes only CASE STYLE: FF99

The Big Deal

- Narrow bandwidth
- Good VSWR (1.4:1 typical)
- Fast roll-off

Product Overview

SBP-29+ is a 50Ω bandpass filter in a connectorized package. This bandpass filter covers from 24 to 35 MHz, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages		
High rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band.		
Good VSWR, 1.4:1 typical over passband	This provides well matched input and output ports.		
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.		

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warnantly and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 24 to 35 MHz



Generic photo used for illustration purposes only

Unit

dВ

:1

dB

:1

CASE STYLE: FF99 Connectors Model

SBP-29+

27

50

27

26

20

20


Features

- · Good VSWR, 1.4:1 typical over passband
- High rejection, 40dB
- · Connectorized package


Applications

- Receivers / Transmitters
- · Harmonic rejection
- Test equipment
- Military

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings Operating Temperature -40°C to 85°C Storage Temperature RF Power Input 0.25 W max.

Insertion Loss

Insertion Loss

Insertion Loss

VSWR

VSWR

VSWR

Parameter

Pass Band

Stop Band, Lower

Stop Band, Upper

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Electrical Specifications at 25°C

F1-F2

F1-F2

DC-F3

DC-F3

F4-F5

F4-F5

Frequency (MHz)

24 - 35

24 - 35


DC - 18


DC - 18


46 - 1600


46 - 1600

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1.0	99.98	3041.22	24.0	117.53
10.0	72.54	1099.97	24.5	108.21
15.0	45.80	313.46	25.0	98.61
18.0	29.01	101.39	25.5	90.82
19.5	19.35	44.23	26.0	85.03
22.0	2.91	2.80	26.5	80.65
24.0	0.85	1.10	27.0	77.21
29.0	0.64	1.07	27.5	74.47
35.0	0.88	1.13	28.0	72.24
39.0	3.37	3.16	28.5	70.44
44.0	20.24	37.43	29.0	68.96
46.0	25.97	53.75	29.5	67.73
48.0	30.89	68.84	30.0	66.70
60.0	51.07	134.78	30.5	65.83
100.0	79.23	225.23	31.0	65.12
200.0	93.07	227.20	31.5	64.62
500.0	79.30	145.38	32.0	64.32
600.0	74.38	122.49	32.5	64.28
1000.0	59.80	57.36	33.0	64.52
1600.0	46.04	7.35	35.0	69.08









- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.js;

SBP-29+ Bandpass Filter

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

Wt.	E	D	В
grams	.312	1.98	.70
42 0	7 92	50 29	17 78

Note: Please refer to case style drawing for details



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp