3 Way-0°  $75\Omega$  5 to 1500 MHz

# **The Big Deal**

- Wideband, 5 to 1500 MHz
- Low insertion loss, 1.0 dB
- · High isolation, 24 dB



CASE STYLE: AH202

# **Product Overview**

Mini-Circuits' SYPS-3-152-75+ is a  $75\Omega$  3-way 0° surface mount splitter/combiner covering the 5 to 1500 MHz frequency range, supporting bandwidth requirements for DOCSIS® 3.1 systems and equipment as well as other broadband applications. This model can handle up to 1W RF input power as a splitter and provides low insertion loss, high isolation, and low phase and amplitude unbalance. It comes housed in a miniature, 8-lead plastic package (0.38 x 0.50 x 0.25") with wrap-around terminations for excellent solderability and gold over nickel plate termination finish.

# **Key Features**

Feature	Advantages				
Wideband, 5 to 1500 MHz	Suitable for many broadband applications including DOCSIS® 3.1 systems and equipment.				
Low insertion loss, 1.0 dB	The combination of 1W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining signal power.				
Low unbalance:  • 0.2 dB amplitude unbalance  • 2.0° phase unbalance	SYPS-3-152-75+ produces nearly equal output signals, ideal for parallel path / multichannel systems.				
Good isolation, 24 dB	Minimizes interference between input ports.				
Good VSWR, 1.2:1 typ.	Provides excellent thru-path transmission with low signal reflection.				

# Surface Mount Ower Splitter/Combiner syps-3-152-75+ /ay-0° 75Ω 5 to 1500 MHz

#### **Features**

- low insertion loss 1.0 dB typ.
- good isolation, 24 dB typ.
- wide frequency band, 5 to 1500 MHz
- low amplitude unbalance, 0.4 dB typ.
- low phase unbalance, 2.0 deg. typ.

#### **Applications**

- CATV
- VHF/UHF
- cellular
- DOCSIS 3.1system



Generic photo used for illustration purposes only

CASE STYLE: AH202

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



#### Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1500	MHz	
	5-50	_	0.6	1.3		
Insertion Loss, above 4.8 dB	50-1220	_	0.8	1.8	dB	
	1220-1500	_	1.9	2.9		
	5-50	23	27	_		
Isolation	50-1220	16	24	_	dB	
	1220-1500	13	18	_		
Phase Unbalance	5-870	_	1.5	5.0	Dog	
	870-1500	_	3.0	8.0	Deg.	
	5-50	_	0.2	0.40		
Amplitude Unbalance	50-1220		0.4	0.60	dB	
	1220-1500	_	0.7	1.15		
VSWR (Port S)	5-50	_	1.3	1.65		
	50-1220	_	1.1	1.30	:1	
	1220-1500		1.25	1.80		
VSWR (Port 1 and Port 2)	5-50	_	1.20	1.50		
	50-1220	_	1.25	1.50	:1	
	1220-1500	_	1.30	1.60		

#### **Maximum Ratings**


Parameter	Ratings				
Operating Temperature	-40°C to 85°C				
Storage Temperature	-55°C to 100°C				
Power Input (as a splitter)	1W max.				
Internal Dissipation	0.15 W max.				

Permanent damage may occur if any of these limits are exceeded.

### **Pin Connections**


Function	Pin Number
SUM PORT	8
PORT 1	1
PORT 2	4
PORT 3	5
GROUND	2,3,6,7

#### **Electrical Schematic**






## **Outline Drawing**



### Outline Dimensions (inch)


н	G	F	F	D	C	В	Α
.050	.035	.070	.115	.020	.25	.50	.38
1.27	0.89	1.78	2.92	0.51	6.35	12.70	9.65
1.27	0.09	1.70	2.92	0.51	0.33	12.70	9.00
wt			N	M	L	K	J
grams			.095	.140	.105	.040	.090
0.80			2.41	3.56	2.67	1.02	2.29

#### Demo Board MCL P/N: TB-361+ Suggested PCB Layout (PL-229)



#### NOTE:

- 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.





DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


#### **Typical Performance Data**

Freq. (MHz)	T	otal Los (dB)	s <sup>1</sup>	Amp. Unbal. (dB)	al. (dB)		Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3
	S-1	S-2	S-3		1-2	2-3					
5.00	5.86	5.86	5.86	0.00	29.44	29.16	0.02	1.51	1.40	1.40	1.39
10.00	5.66	5.66	5.66	0.01	31.55	31.39	0.07	1.32	1.30	1.31	1.30
50.00	5.32	5.32	5.31	0.01	30.57	30.91	0.14	1.12	1.22	1.22	1.22
100.00	5.25	5.26	5.24	0.01	29.53	30.06	0.23	1.07	1.20	1.20	1.20
200.00	5.26	5.26	5.25	0.01	28.48	29.54	0.40	1.04	1.19	1.19	1.17
300.00	5.31	5.30	5.30	0.01	27.35	29.16	0.58	1.05	1.19	1.18	1.18
400.00	5.39	5.36	5.37	0.03	26.04	28.50	0.74	1.06	1.19	1.18	1.20
500.00	5.46	5.41	5.44	0.05	24.82	27.84	0.90	1.08	1.19	1.19	1.21
600.00	5.54	5.46	5.52	0.08	23.82	27.32	1.00	1.10	1.19	1.20	1.20
700.00	5.63	5.52	5.60	0.11	23.01	27.03	1.01	1.12	1.20	1.23	1.20
870.00	5.81	5.64	5.77	0.17	21.78	26.53	0.99	1.15	1.27	1.28	1.25
1000.00	5.98	5.74	5.92	0.24	20.94	26.00	0.90	1.20	1.31	1.32	1.29
1200.00	6.32	5.94	6.20	0.38	19.47	23.86	0.59	1.28	1.40	1.39	1.33
1400.00	6.88	6.33	6.65	0.55	17.16	19.36	1.30	1.41	1.52	1.42	1.39
1500.00	7.37	6.70	7.05	0.67	15.46	16.67	2.48	1.52	1.55	1.41	1.38

1. Total Loss = Insertion Loss + 4dB splitter loss







## **Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp