

Engineering Development Model

Power Splitter/Combiner

2 Way-0°

SYPS-ED12879/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : AH202-2

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.5		2600 MHz
Isolation	0.5 - 5 MHz		17	dB
	5 - 1300 MHz		23	dB
	1300 - 2600 MHz		17	dB
Insertion Loss Above 3.0 dB	0.5 - 5 MHz		0.45	dB
	5 - 1300 MHz		0.55	dB
	1300 - 2600 MHz		1.50	dB
Phase Unbalance	0.5 - 5 MHz		0.02	deg.
	5 - 1300 MHz		0.30	deg.
	1300 - 2600 MHz		0.25	deg.
Amplitude Unbalance	0.5 - 5 MHz		0.01	dB
	5 - 1300 MHz		0.02	dB
	1300 - 2600 MHz		0.10	dB
VSWR	SUM Port		1.19	(:1)
	OUT Ports		1.38	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	8
PORT 1	4
PORT 2	5
GROUND	1,2,3,6,7

Functional Diagram

