SFR-SM50+

50Ω DC to 18 GHz SMA-Female to SMA-Male

#### **THE BIG DEAL**

- Low Insertion Loss, 0.14 dB typ. up to 18 GHz
- Excellent VSWR, 1.12:1 typ. up to 18 GHz
- · Low cost adapters, available from stock
- Tri-metal alloy and gold-plated beryllium copper center connector



Generic photo used for illustration purposes only

Model No.	SFR-SM50+			
Case Style	DJ2442-7			
Connectors	SMA-Female to SMA-Male			

# +RoHS Compliant The +Suffix identifies RoHS Compliance. se our website for methodologies and qualifications

# **APPLICATIONS**

Interconnection of RF cable and equipment

#### **PRODUCT OVERVIEW**

Mini-Circuits' SFR-SM50+ is a right-angle SMA-Female to SMA-Male adapter supporting a wide range of applications from DC to 18 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The SFR-SM50+ features Trimetal alloy body and Gold-plated beryllium copper construction center contact.

#### **KEY FEATURES**

Feature	Advantages			
Wideband, DC to 18 GHz	Wide frequency range provides application flexibility and makes this model ideal for broadband and multi-band use.			
Excellent VSWR • 1.12:1 typ. up to 18 GHz	Provides good matching for $50\Omega$ systems and minimizes signal reflections across wide frequency range.			
Low insertion loss • 0.14 dB typ. up to 18 GHz	Provides excellent signal power transmission from input to output.			
Tri-metal alloy and Gold-plated beryllium cop- per construction center contact	Stands up to wear and tear in demanding environments and provides excellent reliability.			
Very wide operating temperature range, • -55 to +100°C	Withstands extreme operating conditions and is suitable for use near high power componentry where heat rise is common.			

REV. B ECO-016626 SFR-SM50+ MCL NY 230126





SFR-SM50+

DC to 18 GHz SMA-Female to SMA-Male

## **ELECTRICAL SPECIFICATIONS AT 25°C**

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		DC		18	GHz
Insertion Loss	DC - 18	_	0.14	_	dB
	DC - 8	_	1.01	1.25	
VSWR	8 - 12	_	1.07	1.25	:1
	12 - 18	_	1.09	1.25	


#### **ABSOLUTE MAXIMUM RATINGS**

Parameter	Ratings		
Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.

50Ω DC to 18 GHz SMA-Female to SMA-Male

## **OUTLINE DRAWING**



Weight: 6.5 grams


Dimensions are in inches (mm). Tolerances: 2 Pl.±.03; 3 Pl. ±.015


# SFR-SM50+

50Ω DC to 18 GHz SMA-Female to SMA-Male

#### **TYPICAL PERFORMANCE DATA**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)		
		SMA-Female	SMA-Male	
10	0.01	1.01	1.01	
100	0.01	1.01	1.01	
1000	0.04	1.01	1.01	
2000	0.03	1.01	1.01	
4000	0.05	1.02	1.03	
6000	0.05	1.02	1.01	
8000	0.03	1.02	1.02	
9000	0.00	1.04	1.04	
10000	0.02	1.07	1.06	
11000	0.00	1.09	1.09	
12000	0.04	1.11	1.12	
15000	0.04	1.06	1.02	
16000	0.04	1.05	1.07	
18000	0.14	1.05	1.12	





#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

