

Coaxial High Pass Filter

50Ω 500 to 3200 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- rugged shielded case
- other standard and custom SHP models available with wide selection of fco

Applications

- lab use
- transmitters/receivers
- radio communications

**SHP-500+
SHP-500**



CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SHP-500(+)	\$38.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

High Pass Filter Electrical Specifications

STOPBAND (MHz)	fco (MHz) Nom.	PASSBAND (MHz)	VSWR (:1)
(loss > 40 dB) (loss > 20 dB)	(loss 3 dB)	(loss < 1 dB)	Stopband Typ. Passband Typ.
DC-280 280-365	454	500-3200	17 1.9


Outline Drawing




Outline Dimensions (inch)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) $\bar{x}$	σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
10.00	73.03	4.97	0.04	100.00	19.48
100.00	91.45	6.05	0.05	150.00	0.55
150.00	74.69	0.45	0.11	200.00	0.67
200.00	63.66	0.50	0.07	250.00	0.99
250.00	52.21	0.65	0.13	290.00	1.21
290.00	42.87	0.80	0.14	297.00	1.26
297.00	41.24	0.83	0.14	350.00	1.66
350.00	28.65	1.12	0.25	355.00	1.72
355.00	27.43	1.15	0.26	365.00	1.88
365.00	24.98	1.21	0.29	385.00	2.33
385.00	19.93	1.36	0.39	390.00	2.49
390.00	18.64	1.40	0.44	451.00	5.83
451.00	3.67	1.22	5.67	456.00	5.80
456.00	2.88	1.04	7.30	480.00	4.48
480.00	0.93	0.26	22.88	485.00	4.18
485.00	0.80	0.17	27.62	490.00	3.92
490.00	0.71	0.11	26.06	495.00	3.68
500.00	0.62	0.04	20.70	500.00	3.48
550.00	0.51	0.02	20.30	550.00	2.43
600.00	0.40	0.01	31.22	600.00	1.92
650.00	0.39	0.00	20.55	650.00	1.57
700.00	0.40	0.01	18.20	700.00	1.33
750.00	0.39	0.01	18.39	750.00	1.17
800.00	0.36	0.01	20.02	800.00	1.05
900.00	0.31	0.01	26.73	900.00	0.88
1000.00	0.29	0.01	28.75	1000.00	0.74
1500.00	0.34	0.00	22.42	1500.00	0.48
2390.00	0.39	0.01	38.09	2390.00	0.37
2840.00	0.46	0.01	25.35	2840.00	0.35
3280.00	0.59	0.01	18.45	3280.00	0.33



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

ALL NEW
minicircuits.com

REV. B
M108326
SHP-500
070308