

Coaxial

Low Pass Filter

50Ω DC to 900 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- good attenuation rate, 1.35 typ. 20dB/ 3dB BW ratio
- rugged shielded case
- other SLP models available with wide selection of cut-off frequencies

Applications

- lab use
- test equipment
- video equipment

SLP-1000+
SLP-1000

CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SLP-1000(+)	\$34.95 ea.	(1-9)


+ RoHS compliant in accordance
with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site
for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-900	990	1340-1750 1750-2000	1.7 18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
10.00	0.01	0.0	10.00	0.77
82.50	0.02	0.0	82.50	0.77
305.00	0.07	0.1	157.50	0.88
525.00	0.17	0.1	230.00	0.83
747.50	0.54	0.1	305.00	0.86
900.00	0.40	0.1	377.50	0.87
930.00	0.75	0.1	452.50	0.89
970.00	2.06	0.2	525.00	0.97
990.00	3.10	0.2	600.00	0.91
1115.00	12.75	0.5	672.50	0.97
1250.00	23.28	0.7	747.50	1.17
1270.00	24.76	0.8	820.00	1.39
1280.00	25.53	0.8	900.00	1.79
1300.00	27.07	0.9	930.00	2.07
1340.00	30.19	1.0	950.00	2.01
1400.00	34.90	1.2	970.00	1.90
1500.00	43.32	1.8	990.00	1.99
1550.00	48.04	2.6	1115.00	1.08
1600.00	53.09	3.9	1190.00	0.76
1700.00	61.90	8.3	1250.00	0.98
1750.00	58.54	3.6	1270.00	0.81
1760.06	58.62	6.4	1280.00	0.34
1790.00	57.18	2.8	1300.00	0.98
1800.00	56.81	1.9	1340.00	0.50
1820.00	55.81	3.2	1400.00	0.80
1850.00	54.77	2.3	1500.00	0.21
1860.00	53.85	1.3	1550.00	0.77
1880.00	53.19	1.8	1600.00	0.55
1900.05	52.56	1.6	1700.00	0.43
1950.00	50.28	1.1	1750.00	0.39



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. A
M98898
SLP-1000
061024