

Coaxial

Low Pass Filter

50Ω DC to 270 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- good attenuation rate, 1.35 typ. 20dB/3dB BW ratio
- rugged shielded case
- other SLP models available with wide selection of cut-off frequencies

Applications

- lab use
- test equipment
- video equipment



CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SLP-300(+)	\$34.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-270	297	410-550 550-1200	1.7 18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

typical frequency response






electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$ σ			
1.00	0.02 0.1	47.4	1.00	2.37
49.00	0.13 0.1	19.7	49.00	2.20
97.00	0.17 0.1	18.2	97.00	2.29
145.00	0.15 0.1	28.3	145.00	2.76
193.00	0.28 0.1	17.5	193.00	2.82
241.00	0.36 0.1	17.4	241.00	3.42
270.00	0.53 0.1	15.6	270.00	4.45
280.00	1.00 0.1	9.8	275.00	5.14
297.00	2.83 0.2	4.3	280.00	5.33
300.00	3.29 0.2	3.8	290.00	5.24
340.00	11.27 0.3	0.7	297.00	5.08
360.00	15.31 0.3	0.4	300.00	4.75
380.00	19.09 0.4	0.3	320.00	3.64
400.00	22.62 0.4	0.2	340.00	2.79
410.00	24.31 0.4	0.2	350.00	2.49
450.00	30.64 0.6	0.1	360.00	1.91
490.00	36.51 0.9	0.1	380.00	1.79
520.00	40.88 1.2	0.1	400.00	1.15
530.00	42.34 1.3	0.1	410.00	0.98
540.00	43.72 1.3	0.1	450.00	0.88
550.00	45.07 1.5	0.1	480.00	0.70
700.00	66.82 5.7	0.1	490.00	1.16
864.00	71.78 6.6	0.1	500.00	0.43
960.00	76.06 6.9	0.1	520.00	2.11
1056.00	70.05 3.2	0.1	530.00	0.67
1110.00	73.87 7.7	0.1	540.00	0.65
1120.00	72.31 5.1	0.1	550.00	0.63
1140.00	76.33 5.1	0.1	700.00	0.61
1150.00	72.33 3.5	0.1	800.00	0.59
1200.00	77.29 5.8	0.1	864.00	0.58



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M98898
SLP-300
070308