

Engineering Development Model

RF Transformer

TC1-ED12760/1

Impedance Ratio : 1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : AT224-3

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		50		300 MHz
Insertion Loss *	3 dB Bandwidth		50 - 300	MHz
	2 dB Bandwidth		50 - 300	MHz
	1 dB Bandwidth		240 - 300	MHz

Notes:

* Insertion Loss is referenced to mid-band loss, 1.44dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	6
PRIMARY	4
SECONDARY	1
SECONDARY CT	3
ISOLATE	2

Configuration : A

