Surface Mount **Bandpass Filter**

50Ω 94 to 108 MHz

The Big Deal

- Flat group delay (10 ns)
- Narrow-band
- Good VSWR (1.2:1 typical)
- Fast roll-off
- Miniature shielded package

Product Overview

The SXBP-101+ is a narrow-band bandpass filter fabricated using SMT technology. Covering 101 MHz ± 7 MHz, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages			
Sharp shape factor	Sharp shape factor helps in adjacent channel rejection and hence increased selectivity.			
Flat group delay (10ns typical)	The model has flat group delay of 10ns which ensures that the signal distortion is very less.			
Good VSWR, 1.2:1 typical over pass- band	This provides well matched input and output ports.			
Small size, 0.44" x 0.74" x 0.27"	The surface mount package enables SXBP-101+ to be used in compact designs.			



SXBP-101+

CASE STYLE: HF1139

- Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

50Ω

94 to 108 MHz

SXBP-101+

CASE STYLE: HF1139


Features

- · Flat group delay over passband
- Good VSWR, 1.2:1 typical in passband
- High rejection, 40 dB
- Shielded case
- Aqueous washable


Applications

- · Test equipments
- · Harmonic rejection
- Transmitters / receivers
- Military

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Parameter F# Frequency (MHz) Min. Max. Unit Typ. Center Frequency 101 MHz Pass Band Insertion Loss F1-F2 94-108 3.5 dB _ 2.3 VSWR F1-F2 94-108 1.2 1.7 :1 Insertion Loss DC-80 dB DC-F3 20 29 Stop Band, Lower _ VSWR DC-F3 DC-80 31 :1 Insertion Loss F4-F5 130-3900 20 27 dB _ Stop Band, Upper F4-F5 VSWR 130-3900 19 :1


Electrical Specifications at 25°C

Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	0.25W max.					

Permanent damage may occur if any of these limits are exceeded

Typical Performance Data at 25°C Insertion Loss (dB) VSWR Frequency **Group Delay** Frequency (MHz) (:1) (MHz) (nsec) 1.0 71.0 94.0 95.0 87.97 86.86 48.97 45.85 46.64 48.26 80.0 28.90 33.42 96.0 43.59 86.0 13.75 11.61 97.0 42.06 88.5 6.98 4.28 98.0 40.80 1.77 99.0 90.5 3.51 39.77 94.0 101.0 1.26 1.08 39.48 38.98 2.15 99.5 100.0 1.79 100.5 108.0 2.05 1.02 38.82 113.0 4.95 3.01 101.0 38.47 9.70 38.29 116.0 6.73 101.5 17.09 13.49 102.0 38.18 120.5 130.0 28.73 24 14 102.5 37 97 200.0 63.19 69.49 103.0 37.89 400.0 85.27 157.93 103.5 37.85 500.0 76 82 157.93 104 0 37 98 1000.0 69.83 75.53 105.0 38.36 2000.0 63.05 51.10 106.0 38.97 3000.0 40.83 38.61 107.0 40 24 3900.0 44.76 18.70 108.0 41.95





Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

,,,,)Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A M160513 SXBP-101+ EDR-10094U RAV/URJ/NY 161230 Page 2 of 3


Bandpass Filter



Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Drawing MCL INDE X PCB Land Pattern \square Ø \boxtimes TY بو د METALLIZATION Ø \boxtimes SOLDER RESIST J TYP 1 1771

Outline Dimensions (inch)

А	В	С	D	Е	F	G
.44	.74	.27	.200	.07	.060	.040
11.18	18.80	6.86	5.08	1.78	1.52	1.02
Н	J	K	L	М		wt
.660	.200	.470	.055	.060		grams
16.76	5.08	11.94	1.40	1.52		3.0

Notes

Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

