

## Engineering Development Model

# RF Transformer

# TCM1.5-ED8438/7

Impedance Ratio : 1.5

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DB714

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	50		2300	MHz
2 dB Bandwidth		50 - 2300		MHz
1 dB Bandwidth		70 - 1900		MHz

### Note:

\* Insertion Loss is referenced to mid-band loss, 0.4dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	4
NOT USED	2,3

### Configuration : D

