RF Transformer

TCM2-1T



CASE STYLE: DB714
PRICE: Contact Sales Dept.

3 to 300 MHz


Maximum Ratings

Operating Temperature	-20°C to 85°C	
Storage Temperature	-55°C to 100°C	
RF Power	0.25W	
DC Current	30mA	
Permanent damage may occur if any of these limits are exceeded.		


Pin Connections

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2
NOT USED	5

Outline Drawing



PCB Land Pattern




Tolerance to be within ±.002

Outline Dimensions (inch)

F	E	D	С	В	Α
.025	.040	.050	.160	.150	.160
0.64	1.02	1.27	4.06	3.81	4.06
wt		K	J.	Н	G
grams		.030	.190	.065	.028
0.15		0.76	4.83	1.65	0.71

Config. A



Features

- excellent amplitude unbalance. 0.2 dB typ.
- excellent phase unbalance, 4 deg. typ. in 1 dB bandwidth
- plastic base with solder plated leads
- aqueous washable

Applications

- impedance matching
- · balanced to unbalanced transformation
- push-pull amplifier


Transformer Electrical Specifications


(Se	Ω RATIO econdary/Primary)	FREQUENCY (MHz)	INSERTION LOSS* 1 dB MHz
	2	3-300	3-300

^{*} Insertion Loss is referenced to mid-band loss, 0.3 dB typ

Typical Performance Data

F	REQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
	3.00	0.44	27.84
	5.00	0.40	29.78
	9.00	0.37	30.87
	30.00	0.38	29.47
	50.00	0.45	28.16
	90.00	0.52	24.71
	150.00	0.55	21.46
	220.00	0.61	18.39
	250.00	0.58	17.86
	300.00	0.74	16.10





Mini-Circuits®

For detailed performance specs