# Bandpass Filter

50Q 1250 to 1560 MHz

## SYBP-1420+



CASE STYLE: TT1423


### **Features**

- · High power handling, 7W
- · Small size
- Temperature stable
- Excellent rejection


### **Applications**

- · Military radio
- Cellular
- GSM
- ISM

### **Functional Schematic**



# **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	1420	_	MHz
Pass Band	Insertion Loss	F1-F2	1250 - 1560	_	2.2	2.9	dB
	VSWR	F1-F2	1250 - 1560	_	1.7	2.2	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 910	20	24	_	dB
Stop Ballu, Lower	VSWR	DC-F3	DC - 910	_	20	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	2000 - 5000	20	25	_	dB
Stop Baild, Opper	VSWR	F4-F5	2000 - 5000	_	10	_	:1


Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	7W* max. at 25°C			


<sup>\*</sup>Passband rating, derate linearly to 3W at 85°C ambient


Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	
1.00	92.10	7043.23	
500.00	48.62	20.02	
700.00	42.08	16.67	
910.00	25.20	13.11	
1000.00	15.22	9.33	
1250.00	2.27	1.72	
1300.00	2.11	1.65	
1400.00	1.91	1.44	
1560.00	2.16	1.68	
1700.00	4.94	2.96	
1800.00	10.68	6.28	
1900.00	20.03	9.67	
2000.00	33.70	11.49	
3000.00	36.90	16.14	
4000.00	35.26	28.97	
5000.00	30.60	21.62	







Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### **Pin Connections**

RF IN	4
RF OUT	6
GROUND	1,2,3,5

### Demo Board MCL P/N: TB-517+ Suggested PCB Layout (PL-308)



### NOTES:


NOIES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B
WITH THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### **Outline Drawing**



### Outline Dimensions (inch )

.25	<b>B</b> . <b>31</b> 7.87	.15	.090	.040	.065	.060	.065
.300	<b>K</b> . <b>060</b> 1.52	.060	.105	.070		g	wt. rams 0.50

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp