

Plug-In Directional Coupler

50Ω

5 to 1000 MHz

TDC-10-2+



Generic photo used for illustration purposes only

CASE STYLE: B02

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature -55°C to 100°C


Storage Temperature -55°C to 100°C

* Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	2
COUPLED	4
GROUND	3
CASE GROUND	3

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F
.480	.500	.240	.255	.210	.230
12.19	12.70	6.10	6.48	5.33	5.84
G	H	J	K	L	wt
.16	.100	.14	.20	.020	grams
4.06	2.54	3.56	5.08	0.51	1.9

Features

- wideband, 5 to 1000 MHz
- excellent directivity, 25 dB typ.
- rugged welded case, hermetically sealed

Applications

- VHF/UHF
- instrumentation
- communication receivers & transmitters




Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W		
			L		M		U		L		M		U			L	MU	
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Max.
5-1000	11.0±0.5	±0.6	1.4	1.8	1.5	1.8	1.6	2.0	50	35	25	20	20	15	1.5	0.5	0.5	


L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]
1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	1.54	11.12	46.98	22.70	15.85	15.65
10.00	1.46	11.07	46.73	23.89	16.30	16.03
20.00	1.48	11.07	46.28	24.86	16.48	16.22
50.00	1.49	11.09	44.93	25.17	16.57	16.32
100.00	1.52	11.13	42.76	25.29	16.72	16.38
200.00	1.59	11.25	37.70	25.93	16.98	16.31
500.00	1.56	11.29	27.82	22.47	17.33	14.79
557.11	1.61	11.38	26.63	21.79	17.30	14.37
972.94	1.72	11.67	18.90	17.81	17.20	12.01
1000.00	1.76	11.75	18.62	17.57	17.20	11.89



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M151107
TCD-10-2+
WZ/TD/CP/AM
200505
Page 1 of 1