

Frequency Mixer

TFM-ED6598/1

Level 17 (LO Power +17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : B13

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	20		2190	MHz
	RF (f _L to f _U)	20		2190	MHz
	IF	90		1515	MHz
Conversion Loss	mid band		6.8		dB
	Total Range		7.4		dB
LO-RF Isolation	Low Range		47		dB
	Mid Range		42		dB
	Upper Range		35		dB
LO-IF Isolation	Low Range		35		dB
	Mid Range		33		dB
	Upper Range		29		dB

Note: Low Range = [f_L to 10f_L] Mid Range = [10f_L to f_U/2] Upper Range = [f_U/2 to f_U]
mid band = [2f_L to f_U/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3