Triplexer

TPLX-E2485+

50 Ω (1-2485 MHz) (1 - 460, 610-1150, 1435-2485 MHz)



CASE STYLE: HR1843

The Big Deal

- Low insertion loss
- 50Ω Impedance
- Miniature shielded package

Product Overview

TPLX-E2485+ is a high performance 50Ω triplexer with the lowpass channel-1 at 1-460 MHz, bandpass channel-2 at 610-1150 MHz and highpass channel-3 at 1435-2485 MHz. The channels are well isolated to minimize inter-channel interference and have minimal insertion loss through their respective bands. The triplexer is built in a shielded package, this triplexer finds its application in satellite communications.

Key Features

Feature	Advantages
Low passband insertion loss, 0.9 dB typical at lowpass and Band pass channel, 0.8 dB typical at the High pass channel	Very low insertion loss ensures less signal loss through all the channels.
Good co-channel rejection	Rejection of 20-50 dB ensures sufficient isolation between the channels
Miniature shielded package	Triplexer is designed into a surface mount package

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Triplexer

TPLX-E2485+

(1 to 2485 MHz) 50Ω (1-460, 610-1150, 1435-2485 MHz)



CASE	CTVI	⊏.	LID1	0.4

Maximum Ratings

Operating Temperature	-40°C to 85°C				
Storage Temperature	-55°C to 100°C				
RF Power Input	2 W				
Permanent damage may occur if any of these limits are exceeded.					

Pin Connections

COMMON PC	RT 16
CHANNEL-1	10
CHANNEL-2	6
CHANNEL-3	20
GROLIND	1 2 3 4 5 7 8 9 11 12 13 14 15 17 18 19

Features


- · Low insertion loss
- 50Ω Impedance
- Miniature shielded package

Applications

- Military
- Satellite communication

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Outline Dimensions (inch mm)

G H		F	E	D	С	В	Α
079 .202		.071	.202	.196	.370	1.200	1.200
2.01 5.13	2	1.80	5.13	4.98	9.40	30.48	30.48
T.GRAMS 8	W		N .159 4.04				

Demo Board MCL P/N: TB-767+ Suggested PCB Layout (PL-409)




Electrical Specifications at 25°C

Para	ameter	Port	Frequency (MHz)	Min.	Тур.	Max.	Unit	
		Low Pass, Channel - 1	1-460	-	0.9	1.7		
	Insertion Loss	Band Pass, Channel - 2	610-1150	-	0.9	1.8	dB	
		High Pass, Channel - 3	1435-2485	-	0.8	1.7		
		Low Pass, Channel - 1	1-460	10	16	-		
Pass Band	Return Loss	Band Pass, Channel - 2	610-1150	9	13	-	dB	
		High Pass, Channel - 3	1435-2485	8	11	-		
		Common	1-460	10	16	-		
			610-1150	9	13	-		
			1435-2485	8	11	-		
		Law Bass Channel 1	610-1150	30	38	-		
		Low Pass, Channel - 1	1435-2485	25	26			
Stop Band Isolation		Band Pass, Channel - 2	1-460	20	29	-	dB	
			1435-2485	20	54	-		
			1-460	45	37	-		
		High Pass, Channel - 3	610-1150	30	34	-		


Typical Performance Data at 25°C


FREQ.	REQ. INSERTION LOSS (dB)				RETURN LOSS (dB)			
(MHz)	Low Pass Chanel -1	Band Pass Chanel -2	High Pass Chanel -3	Common	Low Pass Chanel -1	Band Pass Chanel -2	High Pass Chanel -3	
1.00	0.09	81.12	97.78	47.10	45.95	0.05	0.05	
15.00	0.11	58.07	101.23	30.55	30.59	0.04	0.05	
60.00	0.20	46.11	101.17	20.12	19.96	0.04	0.04	
460.00	0.82	32.61	55.01	26.30	33.46	0.22	0.09	
500.00	2.82	14.63	53.85	6.64	7.05	0.58	0.11	
505.00	3.66	12.76	52.69	5.35	5.64	0.72	0.11	
540.00	19.99	4.53	46.44	3.17	1.25	2.97	0.12	
580.00	30.78	1.04	48.10	12.03	0.72	11.44	0.14	
610.00	41.74	0.58	48.68	31.55	0.57	27.36	0.15	
620.00	46.93	0.57	48.14	21.69	0.54	22.60	0.16	
1100.00	57.84	0.72	42.77	20.77	0.12	19.07	0.82	
1150.00	58.17	0.92	41.86	15.53	0.11	15.14	0.98	
1250.00	54.55	1.39	18.41	31.72	0.11	24.62	1.24	
1435.00	53.28	33.81	0.76	15.91	0.16	0.55	16.38	
1560.00	40.20	38.41	0.51	19.78	7.52	0.41	19.13	
1800.00	58.37	41.59	0.42	18.23	0.15	0.36	18.94	
1950.00	38.86	45.94	0.51	14.19	0.92	0.41	14.44	
2100.00	59.70	47.21	0.53	13.52	0.16	0.43	13.50	
2350.00	50.97	43.23	0.43	15.86	0.16	0.48	15.05	
2485.00	46.91	41.99	0.42	16.55	0.16	0.56	15.14	


Functional Schematic





- Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp















Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Notes
A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp