

Engineering Development Model

RF Transformer


TRS4-ED11435/1

Impedance Ratio : 4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-996


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	0.14		650	MHz
Insertion Loss *	3 dB Bandwidth	0.14 - 650		MHz
	2 dB Bandwidth	3 - 500		MHz
	1 dB Bandwidth	10 - 80		MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.42dB typ.

Configuration : C

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA



PIN CONNECTIONS	
PRIMARY DOT	1
PRIMARY	3
SECONDARY DOT	6
SECONDARY	4
ISOLATED	5
NOT USED	2