# Surface Mount **RF Transformer**

**50**Ω

## 0.08 to 200 MHz


#### **Maximum Ratings**


Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any o	of these limits are exceeded.

#### **Pin Connections**


PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2
NOT USED	5

### **Outline Drawing**





Out	tline	Dime	nsior	ns (i	nch)
A	B	C	D	E	F
.30	.27	.23	.010	.042	.020
7.62	6.86	5.84	0.25	1.07	0.51
G	H	J	K	L	wt
<b>.100</b>	<b>.05</b>	<b>.09</b>	<b>.31</b>	<b>.036</b>	grams
2.54	1.27	2.29	7.87	0.91	0.50



#### **Features**

- wideband, 0.08 to 200 MHz
- excellent return loss
- also available with surface mount gull wing (KK81) plug-in (X65) leads

#### Applications

• VHF • receivers/transmitters



Generic photo used for illustration purposes only CASE STYLE: W38

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### **Transformer Electrical Specifications**

	FREQUENCY (MHz)		INSERTION LOSS*	
		3 dB MHz	2 dB MHz	1 dB MHz
1	0.08-200	.08-200	0.15-150	0.2-80

\*Insertion Loss is referenced to mid-band loss, 0.3 dB typ.

#### **Typical Performance Data**

	FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
	0.05	2.78	1.64	
	0.08	1.18	4.39	
	0.20	0.52	9.45	
	0.50	0.38	16.31	
	1.00	0.36	19.67	
	80.00	0.64	9.96	
	99.33	0.76	8.80	
	150.00	1.23	5.83	
	192.51	1.60	4.60	
	200.00	1.63	4.55	



Notes A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits