RF Transformer

0.01 to 150 MHz

T1-6-KK81+



Generic photo used for illustration purposes only

CASE STYLE: KK81

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	250mW
DC Current	30mA
Darmanant damaga may assur if any	of those limits are avecade

Pin Connections


PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	_
NOT USED	2,5

Outline Drawing



Outline Dimensions (inch)

.05	.05	.100	.020	E . 042 1.07	.010	.23	.27	.30
grams	.100	.050	.125	P .600 15.24	.575	.26	.036	.020



Features

- good return loss
- also available with plug-in (X65) and flat-pack (W38) leads

Applications

- HF/VHF
- receivers/transmitters


Transformer Electrical Specifications


RATIO	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
1	0.01-150	0.01-150	0.02-100	0.05-50

* Insertion Loss is referenced to mid-band loss, 0.15 dB typ.

Typical Performance Data

• • • • • • • • • • • • • • • • • • • •			
FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.01	1.53	3.51	
0.02	0.58	7.36	
0.05	0.18	14.35	
0.10	0.13	20.32	
0.20	0.13	26.00	
50.00	0.54	9.38	
76.89	0.97	6.19	
100.00	1.37	4.61	
143.59	2.26	2.79	
150.00	2.43	2.57	





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuit satandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp