

RF Instrument Amplifier

TVA-63-183A+

50Ω

6 to 18 GHz

Features

- Instrument model with built-in power supply 110/220 VAC
- Gain, 24 dB typ.
- Unconditionally stable
- Output Power, up to 17 dBm typ.
- Excellent Isolation, 62 dB typ.
- Thermally self-protected, LED indicator
- Good matching at input and output
- CE marked



Generic photo used for illustration purposes only

CASE STYLE: PJ2059

Connectors	Model
SMA	TVA-63-183A+

Applications

- Lab use
- Wideband test instrumentation


+RoHS Compliant
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C, unless otherwise noted

Parameter	Condition (GHz)	Min	Typ.	Max.	Units
Frequency Range		6	—	18	GHz
Gain	6 - 18	20	24	—	dB
Gain Flatness	6 - 18	—	±1.5	—	dB
Output Power at 1dB compression	6 - 18	15	17	—	dBm
Noise Figure	6 - 18	—	6.4	—	dB
Output third order intercept point	6 - 18	—	26	—	dBm
Input VSWR	6 - 18	—	1.5	—	:1
Output VSWR	6 - 18	—	1.25	—	:1
AC Supply Voltage	47 - 63 Hz	85	110/220	265	V

Note: Keep area adjacent to the airvents clear to allow free air flow.

Outline Drawing



Maximum Ratings

Parameter	Ratings
Operating Temperature	0°C to 55°C
Storage Temperature	-40°C to 70°C
Input RF Power (no damage)	+20 dBm

Permanent damage may occur if any of these limits are exceeded.

Outline Dimensions (inch / mm)







A	B	C	D	WT.
15.35	8.27	3.25	3.09	GRAM
389.89	210.06	82.55	78.49	2490

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)	IP3 (dBm)
			IN	OUT			
6000	26.57	37.52	1.24	1.43	6.24	17.69	29.99
6800	26.09	35.82	1.32	1.46	6.25	18.04	29.74
7600	26.01	37.23	1.39	1.44	6.14	17.97	29.37
8400	26.19	39.99	1.35	1.39	6.06	17.76	28.63
9200	26.39	35.49	1.27	1.21	5.99	17.85	28.74
10000	25.85	43.72	1.22	1.15	6.05	17.89	28.85
10800	25.63	36.72	1.12	1.07	6.06	17.77	28.83
11600	25.12	39.61	1.10	1.18	6.04	17.82	28.90
12400	24.58	44.23	1.30	1.31	6.02	17.48	28.96
13200	24.27	44.84	1.44	1.43	6.06	17.32	28.53
14000	24.24	45.00	1.48	1.41	6.17	17.58	27.91
15000	24.28	43.59	1.46	1.30	6.17	17.66	27.64
16000	24.12	46.06	1.37	1.35	6.21	17.64	27.38
17000	23.97	51.94	1.64	1.10	6.20	17.84	27.09
18000	24.07	60.76	1.73	1.09	6.21	17.29	27.07



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

