Surface Mount **RF Transformer**

50Ω

0.015 to 300 MHz


Maximum Ratings

Operating Temperature	-20°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power	0.25W			
DC Current	30mA			
Permanent damage may occur if any of these limits are exceeded.				

Pin Connections

PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2
NOT USED	5

Outline Drawing



Outline Dimensions (inch)								
J	H	G	F	E	D	C	B	A
.05	.05	.100	.020	. 042	.010	.23	.27	.30
1.27	1.27	2.54	0.51	1.07	0.25	5.84	6.86	7.62
wt	S	R	Q	Р	N	M	L	K
grams	. 100	.050	. 125	.600	.575	.26	.036	.020
0.50	2.54	1.27	3.18	15.24	14.61	6.60	0.91	0.51

Config. A C PRI O SEC

Features

- wideband, 0.015 to 300 MHz
- excellent return loss
- also available with plug-in (X65) flat pack (W38) leads

Applications

- VHF/UHF receivers/transmitters
- impedance matching





Generic photo used for illustration purposes only CASE STYLE: KK81

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Transformer Electrical Specifications

Ω RATIO	FREQUENCY (MHz)	INSERTION LOSS*			
		3 dB MHz	2 dB MHz	1 dB MHz	
1	0.015-300	0.015-300	0.021-150	0.03-50	

*Insertion Loss is referenced to mid-band loss, 0.1 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.02	1.24	11.77	
0.13	0.21	26.45	
1.15	0.12	37.26	
47.47	0.40	19.27	
111.99	0.66	14.92	
147.83	0.74	14.64	
175.75	0.75	15.08	
209.75	0.77	16.64	
250.25	0.84	20.06	
300.00	1.09	26.64	



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warrantv and terms and conditions (collectively: "Standard Terms"): Purchasers of this performance

Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance ortheria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp Mini-Circuits