

RF Transformer

T1-ED7122/1

Impedance Ratio : 1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : KK81

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	0.32		567	MHz
Insertion Loss *	3 dB Bandwidth	0.32 - 567		MHz
	2 dB Bandwidth	1-250		MHz
	1 dB Bandwidth	5-100		MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.7dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
NOT USED	2,5

Configuration : C

