

Engineering Development Model

RF Transformer

TX-ED8345/4

Impedance Ratio : 1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TT240

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	0.3		400	MHz
Insertion Loss *				
3 dB Bandwidth		0.3 - 400		MHz
2 dB Bandwidth		0.3 - 350		MHz
1 dB Bandwidth		0.3 - 250		MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.31dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	X1 Y2 Z3
PRIMARY	X6 Y5 Z4

Configuration : F

