

Surface Mount

Voltage Variable Equalizer

VAEQ-1000+

50Ω

50 to 1000 MHz

The Big Deal

- Adjustable attenuation slope
- IP3 +45 dBm typical
- Minimal deviation from linear loss, ± 0.4dB



CASE STYLE: HE1354

Product Overview

The VAEQ-1000+ is a 50Ω Voltage Variable Equalizer built into a shielded case.(size of .394"x.394"x.150") This model offers excellent performance over a wide frequency range of 50 to 1000 MHz with the variable slope providing great flexibility in a small 10mm package.

The VAEQ-1000+ is often used to compensate RF chain gain flatness or cable loss versus frequency.

Key Features

Feature	Advantages
Low power consumption: • Supply voltage +5V _{DC} at max 4mA • Control voltage 0-10V at max 40mA	Allows for high layout density of circuit boards, while minimizing affects of parasitics.
Adjustable attenuation slope (Control voltage of 0V to 10V)	Allows adjusting the slope to compensate for the precise loses encountered.
High linearity (IP3 +45 dBm typ.)	Low distortion enabling improved system performance.
Minimal deviation from linear loss over frequency range: ±0.4dB	Provides low signal distortion over the passband.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount

Voltage Variable Equalizer

50Ω

50 to 1000 MHz

VAEQ-1000+

Features

- Wide bandwidth
- Low insertion loss
- Low deviation from linear loss, ± 0.4 dB typ.
- High IP3 +45 dBm typ.
- Shielded case
- Aqueous washable



CASE STYLE: HE1354

Applications

- Cable loss compensation
- Instrumentation

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C, $V_+=5V_{DC}$ unless otherwise noted

Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range		50		1000	MHz
Insertion Loss	50 MHz, Control Voltage, 0 - 10V 1000 MHz, Control Voltage, 0 - 10V		15.2 - 2.2 1.7 - 1.6		dB
Deviation from Linear Loss	50 - 1000 MHz, Control Voltage 0 - 10V		± 0.4		dB
IP3	50 - 1000 MHz, Control Voltage, 1 - 10V	+33	+45		dBm
1 dB Compression	50 - 1000 MHz, Control Voltage, 0 - 10V		+30		dBm
Input Return Loss ¹	50 - 1000 MHz, Control Voltage, 0 - 10V		17.5		dB
Output Return Loss ¹	50 - 1000 MHz, Control Voltage, 0 - 10V		17.5		dB
Supply Voltage (V+) ¹	50 - 1000 MHz, Control Voltage, 0 - 10V	3.5	5	5.5	V
Supply Current	50 - 1000 MHz, Control Voltage 10V, 50 - 1000 MHz, Control Voltage 0V,		0 2	4	mA
Control Current	50 - 1000 MHz, Control Voltage 10V 50 - 1000 MHz, Control Voltage 1V		32 0	40	mA


¹ Return Loss may degrade at V+ under 5V.

Maximum Ratings

Parameter	Ratings
Operating Temperature	0°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	+23 dBm
Control voltage	11 V
Supply Voltage (V+)	7 V

Permanent damage may occur if any of these limits are exceeded.

Simplified Functional Diagram



Pad Connections

Function	Pad Number
RF IN	1
RF OUT	6
V CONTROL	3
V+	4
GROUND	2,5

Permanent damage may occur if any of these limits are exceeded.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

REV. B
M151108
VAEQ-1000+
EDR-9802F1
RAV
161213
Page 2 of 5




www.minicircuits.com P.O. Box 35166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Voltage Variable Equalizer

VAEQ-1000+

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	wt.
.394	.394	.150	.122	.075	.098	.038	.038	.026	.051	.038	.046	.434 grams
10.01	10.01	3.81	3.10	1.90	2.49	0.97	0.97	0.66	1.29	0.97	1.17	11.02 0.7

Demo Board MCL P/N: TB-474+

Suggested PCB Layout (PL-285)



- NOTE:
1. TRACE WIDTH IS SHOWN FOR R04350 WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

[Blue Box] DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

[Hatched Box] DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Pad Connections

Function	Pad Number
RF IN	1
RF OUT	6
V CONTROL	3
V+	4
GROUND	2,5

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

VAEQ-1000+

Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	Vcontrol		Vcontrol		Vcontrol		Vcontrol		Vcontrol		Vcontrol	
	1V	4V	1V	4V	1V	4V	1V	4V	1V	4V	1V	4V
50	15.41	5.11	23.76	23.75	23.68	23.80	0.94	0.89	12.99	-3.65	36.73	45.55
100	14.57	5.11	22.02	23.81	21.89	23.88	0.55	0.73	11.96	-10.63	43.32	44.47
150	13.50	5.13	19.86	23.77	19.68	23.77	0.14	0.55	11.01	-16.83	-	-
200	12.35	5.15	18.02	23.54	17.84	23.49	0.21	0.37	8.33	-22.77	48.87	47.40
250	11.23	5.19	16.44	23.14	16.29	22.99	0.50	0.17	3.88	-28.56	-	-
300	10.17	5.22	15.18	22.65	15.05	22.37	0.66	-0.02	-1.74	-34.16	49.29	45.01
350	9.21	5.26	14.12	21.92	13.97	21.61	0.78	-0.22	-8.58	-39.66	-	-
400	8.33	5.29	13.25	21.00	13.14	20.66	0.78	-0.40	-15.85	-44.83	45.80	45.70
450	7.54	5.30	12.55	19.89	12.41	19.58	0.76	-0.57	-24.03	-49.90	-	-
500	6.80	5.27	12.01	18.65	11.86	18.42	0.63	-0.71	-32.20	-54.56	43.01	44.22
550	6.16	5.19	11.59	17.30	11.46	17.19	0.50	-0.78	-41.09	-59.11	-	-
600	5.54	5.02	11.34	15.93	11.19	15.92	0.30	-0.77	-49.87	-63.47	44.56	48.98
650	4.98	4.75	11.22	14.61	11.14	14.69	0.10	-0.67	-59.08	-68.00	-	-
700	4.44	4.36	11.31	13.45	11.21	13.63	0.10	-0.43	-68.37	-73.10	42.19	44.52
750	3.91	3.96	11.60	12.56	11.64	12.84	0.28	-0.20	-77.81	-78.85	-	-
800	3.37	3.51	12.27	12.05	12.32	12.42	0.40	0.10	-87.66	-85.55	45.44	45.81
850	2.79	3.19	13.42	11.98	13.61	12.46	0.58	0.26	-98.04	-92.48	-	-
900	2.18	2.72	15.28	12.60	15.87	13.20	1.00	0.57	-109.81	-99.58	46.64	47.10
1000	1.60	1.77	14.51	14.10	15.74	14.96	0.00	1.20	-138.90	-119.98	45.32	48.95

Frequency (MHz)	Insertion Loss (dB)		Input Return Loss (dB)		Output Return Loss (dB)		Deviation from Linear Loss (dB)		Insertion Phase (deg)		Input IP3 (dBm)	
	Vcontrol		Vcontrol		Vcontrol		Vcontrol		Vcontrol		Vcontrol	
	7V	10V	7V	10V	7V	10V	7V	10V	7V	10V	7V	10V
50	2.38	2.10	29.54	28.70	29.41	28.76	0.36	0.36	-3.66	-3.28	41.08	46.48
100	2.36	2.08	30.69	35.57	30.28	35.64	0.35	0.35	-11.56	-11.54	48.68	47.18
150	2.37	2.10	29.99	42.01	29.55	41.01	0.31	0.31	-18.55	-18.73	-	-
200	2.41	2.13	28.88	43.40	28.35	40.52	0.25	0.25	-25.27	-25.63	52.89	46.63
250	2.45	2.17	27.49	37.92	27.11	36.57	0.18	0.18	-31.89	-32.41	-	-
300	2.50	2.22	26.05	33.99	25.73	33.10	0.10	0.10	-38.39	-39.12	53.19	47.62
350	2.57	2.29	24.64	31.00	24.26	30.15	0.00	0.00	-44.83	-45.78	-	-
400	2.67	2.39	23.10	28.28	22.81	27.68	-0.12	-0.12	-51.11	-52.33	54.90	46.51
450	2.76	2.51	21.53	25.79	21.22	25.20	-0.24	-0.24	-57.22	-58.78	-	-
500	2.89	2.68	19.92	23.40	19.61	22.83	-0.40	-0.40	-63.06	-65.00	49.93	45.87
550	3.01	2.86	18.22	20.93	18.01	20.53	-0.54	-0.54	-68.49	-70.83	-	-
600	3.11	3.08	16.49	18.42	16.42	18.23	-0.67	-0.67	-73.32	-75.91	52.74	46.33
650	3.11	3.24	14.81	15.97	14.87	15.97	-0.70	-0.70	-77.60	-79.93	-	-
700	2.90	3.15	13.36	13.87	13.54	14.03	-0.52	-0.52	-81.58	-82.85	48.43	46.04
750	2.55	2.75	12.35	12.44	12.66	12.75	-0.19	-0.19	-86.62	-86.77	-	-
800	2.09	2.18	11.89	11.85	12.26	12.23	0.25	0.25	-93.01	-92.77	51.32	45.98
850	1.83	1.85	11.79	11.77	12.26	12.25	0.48	0.48	-100.90	-100.76	-	-
900	1.62	1.63	11.88	11.89	12.36	12.38	0.66	0.66	-108.80	-108.77	54.44	46.90
1000	1.64	1.64	13.74	13.72	14.42	14.40	0.59	0.59	-121.27	-121.24	51.88	48.86







Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Curves

VAEQ-1000+



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

