

RF Transformer

TC1-1TG2+

 50Ω 0.4 to 500 MHz

FEATURES

- Suitable for tin/lead and RoHS solder systems
- Usable over 0.4-500 MHz
- Excellent amplitude unbalance, 0.1 dB typ. and phase unbalance, 2 deg typ. in 1 dB bandwidth
- Good return loss
- Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: AT224-3

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS•

- VHF/UHF receivers/transmitters
- Push-pull amplifiers

ELECTRICAL SPECIFICATIONS AT 25°C


Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Impedance Ratio			1			
Frequency Range		0.4		500	MHz	
Insertion Loss*	04-500		3			
	0.5-300		2		dB	
	1-100		1			
Phase Unbalance	1-100		2		Deg.	
Phase Oribalance	0.5-300		5			
Amplitude Unbalance	1-100		0.1		dB	
	0.5-300		0.6			


 $^{^{\}star}$ Insertion Loss is referenced to mid-band loss, 0.6 dB typ.

MAXIMUM RATINGS

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25W		
DC Current	30mA		

Permanent damage may occur if any of these limits are exceeded.





SURFACE MOUNT

RF Transformer

TC1-1TG2+


 50Ω 0.4 to 500 MHz

PIN CONNECTIONS

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-145 **SUGGESTED PCB LAYOUT:** PL-244





- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- 3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PÁTTERN FREE OF SOLDER MASK

OUTLINE DRAWING






Suggested Layout, Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inch)

F	Ε	D	С	В	Α
.025	.030	.050	.150	.150	.150
0.64	0.76	1.27	3.81	3.81	3.81
wt		K	J	Н	G
grams		.030	.190	.065	.028
0.10		0.76	4.83	1.65	0.71

TAPE & REEL INFORMATION: F17



RF Transformer


TC1-1TG2+

50Ω 0.4 to 500 MHz

TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)	
0.30	0.88	15.46	0.06	0.03	
1.00	0.57	21.01	0.04	0.05	
5.00	0.33	27.35	0.02	0.01	
10.00	0.32	28.55	0.02	0.15	
50.00	0.40	23.46	0.02	0.63	
100.00	0.51	18.34	0.06	1.24	
200.00	0.78	13.01	0.21	2.57	
300.00	1.10	10.06	0.47	3.99	
400.00	1.46	8.16	0.82	5.66	
500.00	1.84	6.90	1.26	7.50	





NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html