
Coaxial **SMA Fixed Attenuator**

50Ω 0.5W 20dB

Maximum Ratings

| Operating Temperature | -45°C to 100°C | | | | |
|---|----------------|--|--|--|--|
| Storage Temperature | -55°C to 100°C | | | | |
| Permanent damage may occur if any of these limits are exceeded. | | | | | |

Outline Drawing



Outline Dimensions (inch)

| В | D | Е | wt |
|-------|-------|------|-------|
| .410 | 1.43 | .312 | grams |
| 10.41 | 36.32 | 7.92 | 10.0 |

DC to 6000 MHz

Features

- wideband coverage, DC to 6000 MHz
- rugged unibody construction
- off-the-shelf availability very low cost

Applications

- impedance matching
- signal level adjustment



Generic photo used for illustration purposes only

CASE STYLE: FF704 Connectors Model SMA VAT-20+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications


| FREQ. RANGE (MHz) | ATTENUATION * (dB) Flatness ** | | | | VSWR (:1) | | | MAX. INPUT POWER | |
|--------------------------------|--------------------------------------|----------|---------|---------|--------------|-----------|-----------|------------------------|-----|
| | | DC-3 GHz | 3-5 GHz | 5-6 GHz | DC-6 GHz | DC-3 GHz | 3-5 GHz | 5-6 GHz | (W) |
| f _L -f _U | Nom. | Тур. | Тур. | Тур. | Тур. | Тур. Мах. | Typ. Max. | Тур. | |
| DC-6000 | 20±0.3 | 0.45 | 0.55 | 0.35 | 0.85 | 1.05 1.20 | 1.20 1.50 | 1.30 | 0.5 |


Attenuation varies by 0.3 dB max. over temperature.


** Flatness= variation over band divided by 2.

Typical Performance Data Attenuation VSWR Frequency (MHz) (dB) (:1) 0.03 20.08 1.01 20.00 50.00 20.03 20.01 1.00 1.00 100.00 20.02 1.00 500.00 20.11 1.00 1000.00 20.21 1.01 2000.00 20.32 1.06 3000.00 20.10 1.11 4000.00 19.53 1.17 5000.00 18.63 1.24









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warrantv and terms and conditions (collectively: "Standard Terms"): Purchasers of this performance Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

REV. H M151107 VAT-20+ LC/TD/CP/AM 200520 Page 1 of 1