



COAXIAL

Fixed Attenuator

VAT-2W2+

50Ω 2 W 2 dB DC to 6 GHz SMA Female

FEATURES

- Wideband coverage, DC to 6 GHz
- 2 Watt Rating
- Rugged Unibody Construction
- Off-The-Shelf Availability
- Very Low Cost

APPLICATIONS

- Impedance Matching
- Signal Level Adjustment



Generic photo used for illustration purposes only

Model No.	VAT-2W2+
Case Style	DC1066
Connectors	SMA Female

+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range		DC		6	GHz
Attenuation, Nominal			2±0.3		dB
Attenuation ¹ , Flatness ²	DC - 3		0.20		dB
	3 - 5		0.20		
	5 - 6		0.25		
	DC - 6		0.65		
VSWR	DC - 3		1.10	1.20	:1
	3 - 5		1.30	1.50	
	5 - 6		1.50		
Input Power				2.0	W

1. Attenuation varies by 0.3 dB max. over temperature.
 2. Flatness = variation over band divided by 2.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-45°C to +100°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded.


REV. E
 ECO-024278
 VAT-2W2+
 MCL NY
 250122





Fixed Attenuator

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)


B	D	E	wt
.74	1.43	.312	grams
18.80	36.32	7.92	11.4




TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	1.97	1.00
100.00	2.01	1.01
1000.00	2.14	1.05
2000.00	2.23	1.06
3000.00	2.32	1.03
4000.00	2.50	1.04
5000.00	2.64	1.18
5500.00	2.80	1.29
5750.00	2.89	1.36
6000.00	2.96	1.45

VAT-2W2+ ATTENUATION



VAT-2W2+ VSWR



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html