


# Coaxial SMA Fixed Attenuator

50Ω 0.5W 30dB DC to 6000 MHz

## VAT-30+ VAT-30



CASE STYLE: FF704

Connectors	Model	Price	Qty.
SMA	VAT-30(+)	\$11.95 ea.	(1-9)

**+ RoHS compliant in accordance with EU Directive (2002/95/EC)**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

### Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C


### Features

- wideband coverage, DC to 6000 MHz
- rugged unibody construction
- off-the-shelf availability
- very low cost

### Applications

- impedance matching
- signal level adjustment

### Outline Drawing



### Electrical Specifications

FREQ. RANGE (MHz)	ATTENUATION * (dB)					VSWR (:1)					MAX. INPUT POWER (W)
	Flatness **										
	DC-3 GHz		3-5 GHz	5-6 GHz	DC-6 GHz	DC-3 GHz		3-5 GHz	5-6 GHz		
$f_L$ - $f_U$	Nom.	Typ.	Typ.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	
DC-6000	30±0.3	1.10	0.70	0.35	1.30	1.05	1.20	1.15	1.30	1.25	0.5

\* Attenuation varies by 0.3 dB max. over temperature.



\*\* Flatness= variation over band divided by 2.

### Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

### Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
0.03	30.05	1.00
50.00	29.99	1.00
100.00	29.96	1.01
500.00	29.33	1.02
1000.00	28.79	1.04
2000.00	28.77	1.06
3000.00	29.08	1.08
4000.00	29.22	1.03
5000.00	28.72	1.03
6000.00	29.36	1.07



designers kit available

Kit No.	No. of Units in Kit	Description	Price \$ per Kit
K1-VAT	5	1 of ea. VAT-3(+), 6(+), 10(+), 20(+), 30(+)	49.95
K2-VAT	10	1 of ea. VAT-1(+), 2(+), 3(+), 4(+), 5(+), 6(+), 7(+), 8(+), 9(+), 10(+)	99.95
K3-VAT	6	2 of ea. VAT-3(+), 6(+), 10(+)	59.95



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. E  
ED-105218  
VAT-30  
LC/TD/CP/AM  
060829