

Engineering Development Model

RF Transformer

TC1.5-ED8438A/1

Impedance Ratio : 1.5

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.


CASE STYLE : AT224-1A

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		50		2300 MHz
Insertion Loss *	2 dB Bandwidth		50-2300	MHz
	1 dB Bandwidth		70-1900	MHz

Note:

* Insertion Loss is referenced to mid-band loss, 0.70 dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA



PIN CONNECTIONS	
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	4
NOT USED	2,3