# Coaxial **SMA Fixed Attenuator** DC to 6000 MHz


6dB

#### 50Ω **1W**

#### **Maximum Ratings**

Operating Temperature	-45°C to 100°C					
Storage Temperature	-55°C to 100°C					
Permanent damage may occur if any of these limits are exceeded.						

### **Outline Drawing**



### Outline Dimensions (inch )

В	D	Е	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

#### Features

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- off-the-shelf availability
- · very low cost

#### **Applications**

- impedance matching
- signal level adjustment





Generic photo used for illustration purposes only

CASE STYLE: FF704 Connectors Model SMA VAT-6+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Electrical Specifications**


FREQ. RANGE (MHz)	ATTENUATION * (dB) Flatness **				VSWR (:1)			MAX. INPUT POWER	
		DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz	DC-3 GHz	3-5 GHz	5-6 GHz	(W)
f <sub>L-</sub> -f <sub>U</sub>	Nom.	Тур.	Тур.	Тур.	Тур.	Тур. Мах.	Typ. Max.	Тур.	
DC-6000	6±0.3	0.15	0.10	0.20	0.45	1.05 1.20	1.15 1.45	1.50	1.0


\* Attenuation varies by 0.3 dB max. over temperature.


\*\* Flatness= variation over band divided by 2.

#### **Typical Performance Data** Attenuation VSWR Frequency (MHz) (dB) (:1) 0.03 50.00 6.06 1.01 6.01 1 00 100.00 6.02 1.01 500.00 6.10 1.02 1000.00 6.15 1.04 2000.00 6.23 1 04 6.33 1.02 3000.00 4000.00 6.39 1.13 5000.00 6.52 1 29 6000.00 6 94 1 4 5

#### **Electrical Schematic**







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warrantv and terms and conditions (collectively: "Standard Terms"): Purchasers of this performance Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## Mini-Circuits

REV. H M151107 VAT-6+ LC/TD/CP/AM 200520 Page 1 of 1